

เครื่องวัดความหนืด
Digital Lab Viscometer LV DV-2



ติดต่อบริษัท เนโอนิกส์ จำกัด
Tel: 098-479-5684 หรือ 061-8268939
E-mail: sale@neonics.co.th หรือ sale@tools.in.th



LVDV-2 Digital Viscometer

◆ The main technical indicators

Measuring Range (mPa·s)	6 ~ 6,000,000
Rotating Speed (RPM)	0.1 ~ 200(Stepless Gear)
Number of Spindles	Spindles (Code L1,L2,L3,L4) are equipped with the product
Accuracy	±1% full scale range in use
Repeatability	±0.5% full scale range in use
Readability	1.when viscosity is lower than 10.0 cp : 0.01 2.when viscosity is lower than 10000 cp : 0.1 3.when viscosity is equal or higher than 10000 cp : 1
Power	Power adapter (input: 100-240V , 50/60Hz)
LCD screen display	The LCD screen can display the viscosity,speed,torque, spindle and the maximum viscosity can be measured in the current spindle speed value.

◆ Apparatus to be equipped

digital viscosity meter	1 pce	ascending and falling rack	1 set
standard spindle	1 set	power adapter	1 pce
protective frame of spindle	1 pce	spanner	1 pce
Seat and leveling feet	1 set	RS232 standard output interface	1 pce
RTD temperature probe	1 pce		

◆ p ons

• Extreme low viscometer adapter (with one spindle L0)
• Small sample adapter (with spindle 21, 27, 28 and 29 each)
• Temperature-controlled heater (with spindle 21, 27, 28 and 29 each)
• Spindle L5
• Special software that can complete the function in collecting the data automatically
• DV program control download software
• Specially used printer



ติดต่อบริษัท เนโอนิกส์ จำกัด

Tel: 098-479-5684 หรือ 061-8268939

E-mail: sale@neonics.co.th หรือ sale@tools.in.th