

The digital luxmeter is a professional instrument for measuring illumination and brightness, which can be used in light intensity measurement engineering, quality control, illness prevention and treatment and measurement of light intensity in all kinds of environments such as factories, schools, offices, transportation routes, families, etc.

Function			
	WT81	WT81B	
Measure current illumination and temperature	1	1	
Measure difference value, max value and min value	1	V	
Switch between illumination and temperature unit	V	1	
The measurement range is (0~200000) lux, auto switch of measurement gear	1	1	
Automatic storage and manual storage of illumination data	1	$\sqrt{}$	
Setting of automatic power off	√ ·	$\sqrt{}$	
Backlight and data holding	√ \	· \	
Bluetooth	×	1	

Specification			
Measuring function	Illumination and temperature, difference value, max value, min value of illumination		
Main parts of photomet- er head	Photodiode+cosines corrector+correction filter		
Temperature probe	NTC thermistor		
Illuminance measuring range	Total measuring range:0~200,000 Lux,into four ranges ×1:0~199.9 Lux ×10:200~1999.9 Lux ×100:2000~19999.9 Lux ×1000:20000~200000 Lux		
Temperature measuring range	-9.9°C ~ 49.9°C		
Illuminance	±3%rdg (below 10	0000 Lux)	
accuracy	$\pm4\%$ rdg (above 10000 Lux)		
Temperature accuracy	±1.0 °C		
Units of illuminance and temperature	Four combinations of units are available		
	Lux/°C		
	Lux/°F		
	FC/°C		
	FC/°F		
Storage of illumination data	Automatic storage	Max number of data groups is 1000, and storage cycle is set by APP (WT81B)	
	Manual storage	Max number of data groups is 67, and whether to store data is deceived by manual operation.	
Operating temperature/ humidity	0~40°C,10~90%RH		
Storage temperature/ humidity	-10 ~ 50°C, 10 ~ 90%RH		
LCD screen update	2 times/s		
Power source	3* 1.5V AAA batteries		

Application





Factory

Home





Office

School





Photosensitive head



Back screw female design

☑ WT81☑ WT81B

ติดต่อบริษัท นีโอนิคส์ จำกัด

Tel: 02-077-7602 หรือ 061-8268939

E-mail: sale@neonics.co.th เว็บไซต์ www.neonics.biz